



## GS-020S Desktop Ultrasonic Cleaner Machine Numerical Control 3.2L

Our Product Introduction

for more products please visit us on [smtmachinepart.com](http://smtmachinepart.com)

### Basic Information

- Place of Origin: China
- Brand Name: GS
- Model Number: GS-020S
- Minimum Order Quantity: 1 PCS
- Price: USD+negotiable+pcs
- Packaging Details: 280\*180\*250MM
- Delivery Time: 1-7 days
- Payment Terms: T/T
- Supply Ability: 1+pcs+per days



### Product Specification

- Model: GS-020S
- Capacity: 3.2L
- Ultrasonic Frequency: 40KHz
- Transducer: 4 PCS
- Heating Power: 100W
- Ultrasonic Power: 60W/120W
- Time Control: 1-30M
- Size Of Internal Tank: 240\*135\*100MM
- Highlight: Desktop Ultrasonic Cleaner 3.2L,  
Desktop Ultrasonic Cleaner Numerical Control



### More Images



## Product Description

GS-020S desktop numerical control ultrasonic cleaning machine (3.2L) functional features:

1. The operation interface is designed with a 20 degree tilt and controlled by touching the key.
2. High quality ultrasonic transducer, super oscillation, low heating capacity, stable performance and stable output; The intensity of cavitation effect is higher and the cleaning effect is more significant.
3. The inner tank is made of thickened 304 stainless steel, which is formed by one-time stamping without welding; It has good acid and alkali resistance, corrosion resistance, safety and water leakage prevention.
4. High quality components are adopted to perfectly balance the distribution voltage, so that the ultrasonic head can reach the vibration point of the same frequency and achieve stronger resonance effect.
5. More than 6.5l is equipped with stainless steel drain valve, which can easily and quickly discharge the cleaning liquid.
6. It can be used for ultrasonic cleaning, emulsification, mixing, extraction, dispersion, degassing, etc.
7. Accessories: silencing cover, cleaning basket, instruction manual, repair card.

"Functional features of GS-020S high power ultrasonic cleaning equipment (3.2L).

Body: made of high-quality stainless steel, with strong corrosion resistance and long service life;

Inner groove: thickened high-quality stainless steel stamping, no weld, strong waterproof performance;

Time: 1-99 minutes, freely set, suitable for long-time work needs;

Temperature: normal temperature - 80 degrees adjustable, automatic constant temperature heating;

Power: the ultrasonic power is strengthened by one key, the cleaning speed is faster and the effect is cleaner;

Ultrasonic transducer: Industrial transducer, with stronger cleaning force and longer service life;

Drive board: high quality components, double insurance design, short circuit protection, stable performance and high reliability;

Drainage: more than 6.5l is equipped with drainage valve;

Accessories: host, power cord, silencing cover, cleaning basket, manual, warranty card.

In addition, in addition to cleaning, it can also be used for dispersion extraction, nano preparation, chemical reaction, degassing, defoaming, emulsification, mixing, extraction, replacement, catalytic reaction, etc.

Applicable fields: auto parts, printer nozzles, cutting tools, computer motherboards and accessories, laboratory utensils, medical devices, circuit boards, hardware, optical lenses, ticket cards, etc. Glassware, medical equipment, auto parts, circuit board, printer nozzle, hardware and mechanical parts, jewelry, optical lens, ticket card, coin, game coin, etc."

Global Soul Limited

[sales@gs-smt.com](mailto:sales@gs-smt.com)



cleaner machine, Automatic SMT nozzle cleaner, SMT nozzle cleaning equipment, SMT nozzle cleaning process, SMT nozzle maintenance tips, SMT nozzle cleaning services, SMT nozzle cleaning chemicals, SMT nozzle cleaner price, Best SMT nozzle cleaner, How to clean SMT nozzle, SMT nozzle ultrasonic cleaner, SMT nozzle cleaning fluid, SMT nozzle clogging issues, SMT nozzle cleaning tool, Efficient SMT nozzle cleaning, SMT nozzle debris removal, SMT nozzle cleaning tutorial, SMT nozzle cleaning frequency, SMT nozzle cleaner suppliers



**Global Soul Limited**



+8613728696610



liyi@gs-smt.com



smtmachinepart.com

Room F3B-016, B Block, Hao Yun Lai Bussiness Building, Liutang road , Bao'an District , Shenzhen, China